

nVent ERICO Ericore Factory Termination



FEATURES

Upper termination provides an insulated connection from terminal to nVent ERICO Ericore to properly transition the lightning strike

SPECIFICATIONS

Table 1/1

Catalog Number	Length	Length	Termination Location
ERICORE/TERM/IN/MEDIUM	100m	100 - 250 m	Internal
ERICORE/TERM/OUT/MEDIUM	100m	100 - 250 m	External
ERICORE/TERM/IN/LONG		250 - 500 m	Internal
ERICORE/TERM/OUT/LONG		250 - 500 m	External
ERICORE/TERM/OUT/XLONG	500m	500 - 1000 m	External
ERICORE/TERM/IN/XLONG	500m	500 - 1000 m	Internal
ERICORETERMOUSHORT			External

Catalog Number	Length	Length	Termination Location
ERICORE/TERM/IN/SHORT			Internal

ADDITIONAL PRODUCT DETAILS

Termination location can aid in installation. Choose an inner termination location when spool will be delivered to top of structure and conductor pulled to the grounding location.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE