

# Top And Bottom Panels For Floor Standing Enclosures, DPC



Both the enclosure's aesthetics and IP-rating are maintained when a complete set of doors and panels are mounted.

## FEATURES

Description: Required to cover the remaining space at the top and bottom. Used in combination with horizontal dividers CDH/CDHK, partial doors DP, partial panels DPP and cable space door DPA.

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 44. For IP 21 delivered without gasket.

Mounting requirements: DPC covers 200 mm in height of the enclosure. So for a 2000 mm high enclosure when DPC is used, there is 1800 mm space left for partial doors/panels.

Pack quantity: Top and bottom panel with mounting accessories.

SPECIFICATIONS

- Thickness: 1.75mm
- Color: Light Gray
- Material: Mild Steel
- Finish: Powder Coated
- Color Code: RAL 7035

| Table 1/1      |        |       |       |                    |                |            |
|----------------|--------|-------|-------|--------------------|----------------|------------|
| Catalog Number | Height | Width | Depth | Enclosure Material | Product Family | Quick Ship |
| DPC0714R5      | 104mm  | 400mm | 17mm  | Mild Steel         | Free-Standing  | No         |
| DPC0716R5      | 104mm  | 600mm | 17mm  | Mild Steel         | Free-Standing  | No         |
| DPC0718R5      | 104mm  | 800mm | 17mm  | Mild Steel         | Free-Standing  | No         |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE