NGC-30 Series, MONI-RMC Remote Base Module

nVent RAYCHEM remote modules for control (RMC) provide multiple relay outputs for switching heating cable circuits controlled by the nVent RAYCHEM NGC User Interface Terminal (NGC-UIT). RMC units are modular and may be configured with 2 to 40 relay outputs. A single nVent RAYCHEM NGC-30-UIT can communicate with up to 10 RMC via a single, twisted pair RS-485 cable to provide distributed control of up to 260 heating cable circuits.

FEATURES

- 2 digital inputs per DI module
- 2 relay outputs per RO module
- Up to 20 DI and 20 RO modules per RMC-Base module
- Each base module has its own modbus address

SPECIFICATIONS

Mounting: DIN Rail

Table 1/1

Catalog Number	Item Name	Height	Width	Depth
920455-000	RMC-2RO	100 mm	12 mm	100 mm
062367-000	RMC-2DI	100 mm	12 mm	80 mm
309735-000	RMC-BASE	100 mm	80 mm	100 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa
Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific
Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America
Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:
RAYCHEM PYROTENAX TRACER NUHEAT