

Varistar CP Cabeling Rack, RAL 7021, Medium Density, 42 U, 2000H, 800W, 1200D

CATALOG NUMBER

10630-027



Welded steel frame for high static load requirments.
Prepared for high cable densities and 19" integration.

FEATURES

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different Networking equipment possible

Integrated vertical and horizontal cable management

Can be easily integrated into aisle containment system

PRODUCT ATTRIBUTES

Product Family: Varistar CP

Rack Height: 42U

Cladding Material: Steel

Frame Color: Black Grey

Height: 2000mm

Frame Color Code: RAL 7021

Cladding Color: Black Grey

Width: 800mm

Depth: 1200mm

Static Load: 1600kg

Cladding Color Code: RAL 7021

Package Quantity: 1

Dynamic Load: 1000kgf

Finish: Powder Coated

Frame Material: Steel

Material: Steel

Product Type: Rack

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE