


PSU 19" for CompactPCI, AC/DC, 6 U, 8 HP

CATALOG NUMBER

13100-145



Pluggable 19" Power Supply with P47 connector, for CompactPCI applications.

CERTIFICATIONS



FEATURES

Connector P47 and CompactPCI signalling

4 output voltages

Redundant operation with Current Share Bus (CSB), hot-swap

PRODUCT ATTRIBUTES

Product Type: Power Supply

Type: 19" Switched-Mode

Works With: CompactPCI and VME64x

Input Voltage AC: 90 – 264V

Power: 500W

Number of Output Voltages: 4

Voltage 1: 5V

Current 1: 50A

Voltage 2: 3.3V

Current 2: 60A

Voltage 3: 12V

Current 3: 12A

Voltage 4: -12V

Current 4: 4A

Rack Height: 6U

Rack Width: 8HP

Depth: 171.93mm

Net Weight: 1.5kg

Package Quantity: 1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE