

Combined Mounting Kit for Chassis, 20:62 HP

CATALOG NUMBER

24562-420



The combined mounting enable the option to split a 6 U high subrack or case in 2 x 3 U and 6 U sections. Different versions are available.

CERTIFICATIONS



FEATURES

Designed to accept Euroboards (100 mm high) and double Euroboards (233.35 mm high)

Subdivision of the 6 U assembly area into: 2 x 3 U, 1 x 6 U

PRODUCT ATTRIBUTES

Package Quantity: 1

Rack Width 1: 20HP

Rack Width 2: 62HP

Material: Aluminum; Zinc Alloy

Product Family: EuropacPRO

Product Type: Mounting Kit

Rack Height: 6U

Type: Combined

Works With: Subracks

ADDITIONAL PRODUCT DETAILS

Please order separately: Front panel 6 U, 2 HP to cover the strut.

The following guide rails cannot be used: type "accessory", type "accessory, strengthened" and type "for 4.4" PCB".

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE