

Varistar CP Plain Steel Door, Seismic EMC and IP55, Multi-Point Locking



EMC and IP55 Steel Door with lever handle and 4-Point locking.

FEATURES

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for Seismic & EMC applications

SPECIFICATIONS

Product Type: Cabinet Door

Protection Rating: IP55

Material: Steel

Table 1/2

Catalog Number	Rack Height	Height	Width	Package Quantity	Complies With	Finish
21630-760	33U	1600mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Powder Coated
21630-761	33U	1600mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Powder Coated

CatalogNumber	Rack Height	Height	Width	Package Quantity	Complies With	Finish
21630-762	38U	1800mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Powder Coated
21630-763	38U	1800mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Powder Coated
21630-764	42U	2000mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Powder Coated
21630-765	42U	2000mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Powder Coated
21630-766	47U	2200mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Powder Coated
21630-767	47U	2200mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Powder Coated

Table 2/2

Catalog Number	Locking Type	Type	Works With	Quick Ship
21630-760	4-Point Locking	Steel Door, Plain	Varistar CP	No
21630-761	4-Point Locking	Steel Door, Plain	Varistar CP	No
21630-762	4-Point Locking	Steel Door, Plain	Varistar CP	No
21630-763	4-Point Locking	Steel Door, Plain	Varistar CP	No
21630-764	4-Point Locking	Steel Door, Plain	Varistar CP	No
21630-765	4-Point Locking	Steel Door, Plain	Varistar CP	No
21630-766	5-Point Locking	Steel Door, Plain	Varistar CP	No

Catalog Number	Locking Type	Type	Works With	Quick Ship
21630-767	5-Point Locking	Steel Door, Plain	Varistar CP	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE