

## Varistar CP Swing Frame for 800 mm Width



The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° / 160° movement and flexible pivot point.

### FEATURES

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks

120° / 160° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

Usable height within the swing frame is 4U lesser than the frame height to which the swing frame is attached to.

## SPECIFICATIONS

**Width:** 800mm  
**Product Type:** Cabinet/Rack Frame  
**Material:** Steel

Table 1/2

| Catalog Number | Angle    | Rack Height | Package Quantity | Color      | Color Code | Finish        |
|----------------|----------|-------------|------------------|------------|------------|---------------|
| 21630-669      | 120° min | 24U         | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-671      | 120° min | 29U         | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-673      | 120° min | 33U         | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-675      | 120° min | 38U         | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-677      | 120° min | 42U         | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-679      | 120° min | 47U         | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-680      | 160° min | 24U         | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-681      | 160° min | 29U         | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-682      | 160° min | 33U         | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-683      | 160° min | 38U         | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-684      | 160° min | 42U         | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-685      | 160° min | 47U         | 1                | Black Grey | RAL 7021   | Powder Coated |

Table 2/2

| Catalog Number | Height | Protection Rating | Quick Ship |
|----------------|--------|-------------------|------------|
| 21630-669      | 1200mm | IP20              | No         |

| Catalog Number | Height | Protection Rating | Quick Ship |
|----------------|--------|-------------------|------------|
| 21630-671      | 1400mm | IP20              | No         |
| 21630-673      | 1600mm | IP20              | No         |
| 21630-675      | 1800mm | IP20              | No         |
| 21630-677      | 2000mm | IP20              | No         |
| 21630-679      | 2200mm | IP20              | No         |
| 21630-680      | 1200mm | IP20              | No         |
| 21630-681      | 1400mm | IP20              | No         |
| 21630-682      | 1600mm | IP20              | No         |
| 21630-683      | 1800mm | IP20              | No         |
| 21630-684      | 2000mm | IP20              | No         |
| 21630-685      | 2200mm | IP20              | No         |

## ADDITIONAL PRODUCT DETAILS

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**