

# Intelligent PDU, EN5xxx, 230 VAC, 1-PH

## Data Solutions

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



### FEATURES

Enlogic EN5xxx Intelligent Power Distribution Units monitors input power of the entire PDU and individual outlet monitoring, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

### SPECIFICATIONS

Table 1/6

Catalog Number	Product Family	Type	Product Type	Socket Type	Socket Quantity	Color
EN5403	Enlogic	Intelligent PDU	Socket Strip	(30) C13, (6) C19	36	Black
EN5325	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN5329	Enlogic	Intelligent PDU	Socket Strip	(24) C13, (8) C19	32	Black
EN5337	Enlogic	Intelligent PDU	Socket Strip	(38) C13, (6) C19	44	Black

Table 2/6

Catalog Number	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Current Rating	Power Rating	Input Cable Location
EN5403	16 A, 1-pole, Hy-Mag	No	0			Top Feed
EN5325	16 A, 1-pole, Hy-Mag	No	2		7.4 kVA	Top Feed
EN5329	16 A, 1-pole, Hy-Mag	No	2		7.4 kVA	Top Feed
EN5337	16 A, 1-pole, Hy-Mag	No	2	32A		Top Feed

Table 3/6

Catalog Number	Input Voltage	Phase	Interrupt Rating	Max Power Input	Nominal Voltage	On/Off Switch Included
EN5403	400V	3 PH WYE	5kAIC	11.0 kVA		
EN5325	200 – 240V	1 PH	5kAIC	7.44 kVA	230V	No
EN5329	200 – 240V	1 PH	5kAIC	7.44 kVA	230V	No
EN5337	200 – 240V	1 PH	5kAIC	7.44 kVA		

Table 4/6

Catalog Number	Output Voltage	Amperage (Derated Amperage)	Plug Type	Rack Units	Removable Input Cable	Metering Type
EN5403	200 – 240VAC	32 A	IEC 60309 516P6 (IP44)	0U	No	Outlet
EN5325	230VAC	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet
EN5329	230VAC	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet
EN5337	200 – 240VAC	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet

Table 5/6

Catalog Number	Material	Finish	Height	Width	Depth	Weight
----------------	----------	--------	--------	-------	-------	--------

EN5403						
EN5325	Steel	Powder Coated	1780mm	52mm	53mm	8.82kg
EN5329	Steel	Powder Coated	1780mm	52mm	53mm	8.52kg
EN5337						

Table 6/6

Catalog Number	Package Quantity	Input Cable Length
EN5403	1	
EN5325	1	3m
EN5329	1	3m
EN5337	1	

## ADDITIONAL PRODUCT DETAILS

---

Please order bracket for vertical mounting separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**