

Varistar CP Double Steel Door, Plain, 3-Point Locking

Power Utilities

Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

FEATURES

Double steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Height	Width	Color	Color Code	Complies With
21630-086	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-087	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-088	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-089	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-090	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-091	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-440	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

CatalogNumber	Rack Height	Height	Width	Color	Color Code	Complies With
21630-441	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-442	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-443	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-444	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-445	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-446	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-447	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Catalog Number	Locking Type	Product Type	Protection Rating	Type	Works With
21630-086	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-087	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-088	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-089	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-090	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-091	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-440	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-441	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-442	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-443	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP

Catalog Number	Locking Type	Product Type	Protection Rating	Type	Works With
21630-444	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-445	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-446	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-447	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE