

# Cable/Conduit to Wire Clip



## CERTIFICATIONS



## FEATURES

Supports cable and conduit without bending drop wire

Faster installation than traditional methods

## SPECIFICATIONS

**Finish:** nVent CADDY Armour

**Material:** Spring Steel

Table 1/1

Catalog Number	Article Number	Outer Diameter (OD)	Wire Size	Hole Size (HS)	Ultimate Static Load (F)	Certifications
PCS2	170881	15 - 23 mm	2 - 4 mm	6.8 mm	110N	ITB
PCS1	170880	11 - 14 mm	2 - 4 mm	6.8 mm	110N	cUL, UL, ITB


## ADDITIONAL PRODUCT DETAILS

---

NEC® 300.11 requires dedicated drop wire/rod and EC311.

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

