

# IceStop Self-Regulating Heating Cable

## Data Solutions



nVent RAYCHEM IceStop self-regulating trace heating cables provide roof and gutter de-icing, suitable for all standard materials of gutters and drainpipes. Power output is 36 W/m at 0 °C in ice water, 18 W/m at 0 °C in air.

## FEATURES

Simple to design

Easy to install: cut to length, meter marks, simple fast RayClic connections

Safe and efficient in operation: no overheating, even when crossed, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

GM-2XT for bitumen roofs

## SPECIFICATIONS

|                                      |                      |
|--------------------------------------|----------------------|
| <b>Nominal Thickness:</b>            | 6mm                  |
| <b>Nominal Width:</b>                | 14mm                 |
| <b>Nominal Cable Weight:</b>         | 130g/m               |
| <b>Supply Voltage:</b>               | 208 – 240V           |
| <b>Min Installation Temperature:</b> | -18°C                |
| <b>Color:</b>                        | Black                |
| <b>Ground Path Type:</b>             | Braid                |
| <b>Conductor Material:</b>           | Nickel-Plated Copper |

Table 1/1

| Catalog Number | Article Number | Nominal Power Output, In Air @ 0°C, 230V | Nominal Power Output, In Ice Water @ 0°C, 230V | Outer Jacket Material |
|----------------|----------------|------------------------------------------|------------------------------------------------|-----------------------|
|----------------|----------------|------------------------------------------|------------------------------------------------|-----------------------|

|            |        |       |       |                     |
|------------|--------|-------|-------|---------------------|
| 092961-000 | GM-2XT | 18W/m | 36W/m | Fluoropolymer       |
| 446105-000 | GM-2X  | 18W/m | 36W/m | Modified Polyolefin |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE