

## Rain Hood, ARF



A mild steel rain hood provides shelter via a sloped roof and protects installed components from accumulated water dripping into the enclosure when the door is opened.

### FEATURES

---

Description: To be fitted as an outdoor shelter on single mounted enclosures. The roof is slightly sloped and has a dripstrip. Machining is required. It increases the enclosure dimension in H:60 mm, D:20 mm and W:20 mm.

Material: 1.5 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 rain hood with mounting accessories.

Additional information: For exposure to high levels of UV radiation, the ARF should be ordered with 100% polyester paint coating. An additional corrosion protection primer coating is recommended for humid environments. Resistance to corrosion must be taken into consideration for outdoor and indoor applications. The ARF is not compatible with 180° MMH hinges.

## SPECIFICATIONS

**Thickness:** 1.5mm  
**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

Table 1/1

Catalog Number	Height	Width	Depth	Enclosure Material	Product Family	Quick Ship
ARF02515R5	55mm	250mm	155mm	Mild Steel	Wall Mounted	No
ARF02521R5	60mm	250mm	210mm	Mild Steel	Wall Mounted	No
ARF03015R5	55mm	300mm	155mm	Mild Steel	Wall Mounted	No
ARF03021R5	60mm	300mm	210mm	Mild Steel	Wall Mounted	No
ARF04015R5	55mm	400mm	155mm	Mild Steel	Wall Mounted	No
ARF04021R5	60mm	400mm	210mm	Mild Steel	Wall Mounted	No
ARF04026R5	65mm	400mm	260mm	Mild Steel	Wall Mounted	No
ARF04030R5	68mm	400mm	300mm	Mild Steel	Wall Mounted	No
ARF05015R5	55mm	500mm	155mm	Mild Steel	Wall Mounted	No
ARF05021R5	60mm	500mm	210mm	Mild Steel	Wall Mounted	No
ARF05026R5	65mm	500mm	260mm	Mild Steel	Wall Mounted	No
ARF05030R5	68mm	500mm	300mm	Mild Steel	Wall Mounted	No
ARF06021R5	60mm	600mm	210mm	Mild Steel	Wall Mounted	No
ARF06026R5	65mm	600mm	260mm	Mild Steel	Wall Mounted	No
ARF06030R5	68mm	600mm	300mm	Mild Steel	Wall Mounted	No
ARF06040R5	77mm	600mm	400mm	Mild Steel	Wall Mounted	No

Catalog Number	Height	Width	Depth	EnclosureMaterial	Product Family	Quick Ship
ARF08021R5	60mm	800mm	210mm	Mild Steel	Wall Mounted	No
ARF08026R5	65mm	800mm	260mm	Mild Steel	Wall Mounted	No
ARF08030R5	68mm	800mm	300mm	Mild Steel	Wall Mounted	No
ARF08040R5	77mm	800mm	400mm	Mild Steel	Wall Mounted	No
ARF10030R5	68mm	1000mm	300mm	Mild Steel	Wall Mounted	No
ARF12030R5	68mm	1200mm	300mm	Mild Steel	Wall Mounted	No

## ADDITIONAL PRODUCT DETAILS

---

Not suitable for AFS.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**