nVent | SCHROFF

We connect and protect

Connector Keying/Coding Contact Strip for All Types, EN 60603, DIN 41612

CATALOG NUMBER

20800-042



Connector coding is used to provide security against incorrect insertion.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

- Use with plug-in units to avoid incorrect insertion
- For connectors in accordance with EN 60603 (DIN 41612)
- Needed space is front panel width: 4 HP: Type B, C, D, E, F, H
- Needed space of front panel width: 5 HP: Type E, G (Spacer element is required)
- 66 keying/coding possibilities if 2 keying/coding pins are used
- 924 keying/coding possibilities if 6 keying/coding pins are used

PRODUCT ATTRIBUTES

- Product Type: Coding/Keying Indicator
- Material: Polybutylene Terephthalate
- Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

For connectors types E and G spacers are always required.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.