


PHSW Multi-Purpose Purlin Clamp with Swivel



CERTIFICATIONS



FEATURES

Attachment to bottom of purlins and beams to support threaded rod

Swivel feature option for attachment to purlins under sloped roofs

SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	Rod Size (RS)	Flange Thickness (FT)	B	Torque (TQ)
PHSW6	Steel	Electrogalvanized	3/8"	6.4 mm Max	19.1 mm Min	40 N·m

Table 2/2


Catalog Number	Static Load 1 (F1)	Static Load 2 (F2)	Nut Included
PHSW6	890N	710N	No

ADDITIONAL PRODUCT DETAILS

A jam nut is required for fire protection applications.

Refer to Static Load 1 when attaching to C and Z purlins. Refer to Static Load 2 when attaching to a flat flange.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

