


Through Roof PVC Assembly, Parallel Conductor to In-Line Conductor



CERTIFICATIONS



FEATURES

Allows for lightning protection conductors to be concealed in ceiling or walls

Use in-line connection for conductor and secure to structure using base plate

SPECIFICATIONS

Conductor Size, UL: Class 1 - Class 2 (4/0 Max)

Table 1/1


Catalog Number	Material	Connection Material, In-Line Conductor	Connection Material, Parallel Conductor	Rod Length (L)	Outer Diameter (OD)	Unit Weight
LPC66524	Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Copper	Copper	660.4mm	48.26 mm	1.45 kg

CatalogNumber	Material	Connection Material, In-Line Conductor	Connection Material, Parallel Conductor	Rod Length (L)	Outer Diameter (OD)	Unit Weight
LPC66524BI	Aluminum, Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Copper	Bi-Metallic	660.4mm	48.26 mm	1.45 kg
LPC66518BI	Aluminum, Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Copper	Bi-Metallic	508mm	48.26 mm	1.25 kg
LPC66518	Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Copper	Copper	508mm	48.26 mm	1.26 kg

ADDITIONAL PRODUCT DETAILS

Always consult the roof manufacturer or owner for proper flashing materials.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including vinyl chloride, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE