

nVent ERIFLEX Zipflex Sleeve



CERTIFICATIONS



FEATURES

Quick and easy screening

Installation tool included

Halogen free

SPECIFICATIONS

Color:	Black
Material:	Polypropylene
Flammability Rating:	UL® 94HB
Working Temperature:	-30 to 140 °C

Table 1/1

Catalog Number	Article Number	Diameter	Length	Unit Weight
ZFX100M8MMBK	554880	8 mm	100m	0.01 kg
ZFX50M15MMBK	554890	15 mm	50m	0.04 kg

Catalog Number	Article Number	Diameter	Length	Unit Weight
ZFX30M20MMBK	554900	20 mm	30m	0.07 kg
ZFX20M25MMBK	554910	25 mm	20m	0.1 kg

ADDITIONAL PRODUCT DETAILS

Unit weight is per meter (3.28').

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE