

Telescope Fitting Lay-in Hinged Cover



Lay-in Hinged Cover Telescope Fitting allows to easily adjust wireway length from 1.00 inch (25 mm) to 7.00 inch (178 mm). No cutting or welding required.

FEATURES

Lay-in Hinged Cover Telescope Fitting allows to easily adjust wireway length from 1.00 inch (25 mm) to 7.00 inch (178 mm)

No cutting or welding required

SPECIFICATIONS

- Color Code:** ANSI 61
- Finish:** Galvanized; Powder Coated
- Color:** Gray
- Material:** Mild Steel

Table 1/1						
Catalog Number	Article Number	Type	Height	Width	Thickness	Sealing Plate Type
F126LA	18960	Telescope Fitting	305mm	152mm	1.9mm	Special
F88LA	19340	Telescope Fitting	203mm	203mm	1.9mm	Special
F44LA	18940	Telescope Fitting	102mm	102mm	1.9mm	Special
F22LA	18930	Telescope Fitting	64mm	64mm	1.9mm	Special
F66LA	18950	Telescope Fitting	152mm	152mm	1.9mm	Special

ADDITIONAL PRODUCT DETAILS

Each sealing plate also includes one gasket and one set of screws to join sections.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE