


EuropacPRO Perforated Rail for Connector



Perforated flat rail for connector mounting i.a.w. EN 60603-2 and DIN 41612, on VT horizontal rails.

CERTIFICATIONS



FEATURES

In conjunction with rear horizontal rails, VT

For Connector Mounting in accordance with EN 60603-2, DIN 41612

SPECIFICATIONS

Material:	Aluminum
Finish:	Passivated
Product Type:	Perforated Rail

Table 1/2

Catalog Number	Rack Width	Package Quantity	Length	Product Family	Works With	Certifications
----------------	------------	------------------	--------	----------------	------------	----------------

20822-052	4HP	4	20.32mm	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	
20822-046	40HP	4	203.2mm	EuropacPRO	Subracks	RoHS
20822-053	8HP	4	40.64mm	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	
20822-051	20HP	4	101.6mm	EuropacPRO	Subracks	RoHS
20822-047	60HP	4	304.8mm	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	RoHS
20822-050	42HP	4	213.36mm	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	RoHS
20822-049	28HP	4	142.24mm	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	RoHS
20822-048	84HP	4	431.8mm	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	RoHS

Table 2/2

Catalog Number	Quick Ship
20822-052	No
20822-046	No

Catalog Number	Quick Ship
20822-053	No
20822-051	No
20822-047	No
20822-050	No
20822-049	No
20822-048	No

ADDITIONAL PRODUCT DETAILS

A threaded insert is required to secure the perforated rail on the horizontal rail.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE