

EBC-133 Earthing and Neutral Busbar



EBC-133 Earthing and Neutral Busbars are used to connect multiple earthing conductors within a panel and can be used in a variety of different applications including switchgear and control equipment, electrical equipment, wind and solar power generation, data centers and in power distribution application.

EBC-133 Earthing and Neutral Busbar can be fixed using IRS Angle Support Bracket, DMH Metallic Spacer or DH Distance Holder and Spacer.

CERTIFICATIONS



FEATURES

Easy for the installer to add connections

Clamps are fully assembled

Clamps follow the screw vertically, making it quick and easy to mount the conductor

Cut to length as needed

Main terminal clamp available for thicker conductors

Can be connected to IBSB25 Insulated Braided Conductor, MJB Grounding and Bonding Braid, and nVent ERIFLEX Flexibar up to 9 mm (0.354")

Quick and easy installation

RoHS compliant

SPECIFICATIONS


Material: Copper;Steel

Finish: Electrogalvanized

Catalog Number	EBC133-10X3X2000	EBC133-15X5X2000
----------------	------------------	------------------

Article Number	568612	568613
Number of Connections	133	133
Conductor Size, IEC	(133) 0.5 - 16 mm ² Solid (133) 0.5 - 10 mm ² Stranded	(133) 0.5 - 16 mm ² Solid (133) 0.5 - 10 mm ² Stranded
Conductor Width	9 mm Max	9 mm Max
Max Current Rating	108A	218A
Cross Section	30mm ²	75mm ²
Depth (D)	10mm	15mm
Width (W)	2000 mm	2000 mm
Thickness (T)	3 mm	5 mm
A	15 mm	15 mm
B	4.8 mm	6.8 mm
Thread Size (TS)	M5	M5
Torque (TQ)	2.5 N·m	4.5 N·m
Unit Weight	1 kg	1.8 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE