


# RackChiller Rack Manifold



RackChiller Rack Manifolds are a configurable solution utilized in liquid cooled applications that require increased uptime and improved power usage effectiveness. Designed with integration and installation in mind, the manifolds utilize plug-and-play style connections, universal mounting features and coexist with other data center accessory equipment.

## FEATURES

Delivers water-based coolant from CDU unit or facility manifolds to cold plate equipment

Standard configuration uses jumper hoses to connect manifold to cold plate equipment (jumper hoses sold separately)

Hose-whip configuration connects directly to cold plate equipment utilizing hose-whips attached directly to the manifold

Various dripless, quick disconnect connectors available to match existing cold plate equipment

Button-style mounting to be used with universal mounting brackets (also used with RackPower PDU products)

Increases data up-time

Extends server equipment life span

Improves data center power usage effectiveness, providing annual return on investment

Multiple connectivity options to match downstream cooling equipment needs

Plug-and-play style installation

Universal mounting features to coexist with other rack accessory equipment (i.e. PDU's, cable management, airflow management, etc.)

Two major configurations designed to service alternate secondary cooling loop products

1.50 x 1.50 (38mm x 38mm) extruded stainless steel construction

Friction-drilled, ORB-6 port threads

Standard manifolds utilize Parker NSP-06 quick disconnect connectors

Eaton FD-83 supply/return ball valve connector

SPECIFICATIONS

| Table 1/1      |                |               |                 |            |       |            |
|----------------|----------------|---------------|-----------------|------------|-------|------------|
| Catalog Number | Article Number | Configuration | Material        | Finish     | Color | Quick Ship |
| RCM42002HQD    | RCM42002HQD    | Hose Whip     | Stainless Steel | Passivated | Black | No         |
| RCM42002QD     | RCM42002QD     | Standard      | Stainless Steel | Passivated | Black | No         |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE