

# Socket Strip, IEC C13, With Wieland® Input



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

## CERTIFICATIONS



## FEATURES

Input via Wieland® GST 18 plug

Installation height 1 U

In accordance with IEC 60320

Horizontal or vertical mounting

Output via IEC 60320 C-13 sockets

Socket strips can be rotated through all four directions (in 90° increments) during fitting

## SPECIFICATIONS

|                      |                     |
|----------------------|---------------------|
| <b>Length:</b>       | 438.5mm             |
| <b>Material:</b>     | Aluminum; Polyamide |
| <b>Product Type:</b> | Socket Strip        |

Table 1/2

| Catalog Number | Socket Type | Socket Quantity | Switched Outlets | Voltage AC | Function | Package Quantity |
|----------------|-------------|-----------------|------------------|------------|----------|------------------|
| 60110-340      | IEC C13     | 12              | No               | 230V       |          | 1                |

| CatalogNumber | Socket Type | SocketQuantity | Switched Outlets | Voltage AC | Function               | Package Quantity |
|---------------|-------------|----------------|------------------|------------|------------------------|------------------|
| 60110-341     | IEC C13     | 12             | No               | 230V       |                        | 1                |
| 60110-342     | IEC C13     | 12             | No               | 230V       |                        | 1                |
| 60110-349     | IEC C13     | 6              | No               | 230V       | Overcurrent Protection | 1                |
| 60110-350     | IEC C13     | 6              | No               | 230V       | Overcurrent Protection | 1                |
| 60110-351     | IEC C13     | 6              | No               | 230V       | Overcurrent Protection | 1                |

Table 2/2

| Catalog Number | Color | Depth | Finish   | Quick Ship |
|----------------|-------|-------|----------|------------|
| 60110-340      | Grey  | 44mm  | Anodized | No         |
| 60110-341      | Black | 44mm  | Anodized | No         |
| 60110-342      | Red   | 44mm  | Anodized | No         |
| 60110-349      | Grey  | 44mm  | Anodized | No         |
| 60110-350      | Black | 44mm  | Anodized | No         |
| 60110-351      | Red   | 44mm  | Anodized | No         |

## ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**