

# nVent ERICO Ericontact Single Rail Contact



The nVent ERICO Ericontact series of rail contacts provides a superior quality connection to the rail web with a very low contact resistance. The contacts are quickly and easily fitted by means of an insertion tool, regardless of weather conditions. All nVent ERICO Ericontact components are manufactured according to high standards and norms. Tested to the most demanding requirements of the Rail Industry Standards, nVent ERICO Ericontact is the ideal solution for mechanically applied connections such as signal engineering, earthing (grounding), or traction return current.

## FEATURES

Easy to install

Very low contact resistance ( $< 5 \mu\Omega$ )

Meets AREMA® Recommendations

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Rail Web Thickness | Rail Type                                                               | Drill Hole Diameter | Screw Diameter (Sc) | Screw Length (L) |
|----------------|----------------|--------------------|-------------------------------------------------------------------------|---------------------|---------------------|------------------|
| SK13518        | 715089         | 14.0 - 18.5 mm     | 136 lb RE, 141 lb AB                                                    | 13.5mm              | 10                  | 55mm             |
| SK1914         | 715050         | 14.0 - 16.9 mm     | 100 lb ARAB, 115 lb AREA, 127 lb NYC, 132 lb RE, 85 lb ASCE, AS50, AS60 | 19mm                | 12                  | 55mm             |
| SK1914L        |                | 14.0 - 16.9 mm     | 100 lb ARAB, 115 lb AREA, 127 lb NYC, 132 lb RE, 85 lb ASCE, AS50, AS60 | 19mm                | 12                  | 70mm             |

| CatalogNumber | Article Number | Rail Web Thickness | Rail Type                                                               | Drill Hole Diameter | ScrewDiameter (Sc) | Screw Length (L) |
|---------------|----------------|--------------------|-------------------------------------------------------------------------|---------------------|--------------------|------------------|
| SK1914SS      | 715051         | 14.0 - 16.9 mm     | 100 lb ARAB, 115 lb AREA, 127 lb NYC, 132 lb RE, 85 lb ASCE, AS41, AS50 | 19mm                | 12                 | 55mm             |
| SK1912        | 715045         | 12.0 - 13.9 mm     | AS41, BHP42, BS90A, RI59, RI60, S41                                     | 19mm                | 12                 | 55mm             |

Table 2/2

| Catalog Number | Article Number | Washer Inner Diameter | Washer Outer Diameter | Nut Material        |
|----------------|----------------|-----------------------|-----------------------|---------------------|
| SK13518        | 715089         | 10.5mm                | 20mm                  | Electroplated Steel |
| SK1914         | 715050         | 13mm                  | 24mm                  | Electroplated Steel |
| SK1914L        |                | 13mm                  | 24mm                  | Electroplated Steel |
| SK1914SS       | 715051         | 13mm                  | 24mm                  | Stainless Steel 304 |
| SK1912         | 715045         | 13mm                  | 24mm                  | Stainless Steel 304 |

## ADDITIONAL PRODUCT DETAILS

Kit includes: (1) hex-head stainless steel 304 bolt, (1) nVent ERICO Ericontact stainless steel 304 SK-washer, (1) electrolytically tin-plated copper bush, (1) stainless steel 304 flat washer, and (1) hexagonal stainless steel 304 nut or (1) electroplated steel nut (depending on contact type).

The washer and nut for SK135165 are integrated into one piece.

## DIAGRAMS



**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**