

# nVent ERICO Lay-In Lock Shear Connector



The nVent ERICO Lay-In Lock Shear Connector features an innovative, tamper-proof solution to tap in and create irreversible parallel connections anywhere on new or existing grounding grids. This quick, low-maintenance option increases convenience and simplifies installation with its shear-off bolt head and unique lay-in feature to hold conductors in place prior to making a secure connection.

Designed to improve performance, reduce damage, and enhance reliability, the nVent ERICO Lay-In Lock Shear Connector ensures a consistent clamp force on every connection. Composed of durable bronze, the unique hexagonal design eliminates the need for specialized tools while allowing installers to meet industry torque requirements and expedite inspection due to its highly visible, permanent connection. Suitable for use with Theft Deterrent Cable and UL listed for #6 and #2 solid cable.

## CERTIFICATIONS



## FEATURES

Hexagonal bolt head shears when proper torque is applied

Lay-in capability eliminates need to feed or cut conductors during installation

Allows for permanent, secure connection between multiple conductors

No special tools required

Suitable for direct burial

Corrosion resistant

Marked to display versatile conductor ranges

RoHS and REACH compliant

Suitable for indoor & outdoor applications

Manufactured in USA

## SPECIFICATIONS

Table 1/2

| Catalog Number | Material | Direct Burial | Conductor Size         | Number of Conductors | Torque | Hex Width |
|----------------|----------|---------------|------------------------|----------------------|--------|-----------|
| ELLC1G         | Bronze   | Yes           | #6 Solid, #6 Stranded  | 2                    | 17 N·m | 16.51 mm  |
| ELLCS1         | Bronze   | Yes           | #6 Solid - #2 Stranded | 2                    | 17 N·m | 19.05 mm  |

Table 2/2

| Catalog Number | Length | Diameter | Unit Weight |
|----------------|--------|----------|-------------|
| ELLC1G         | 50mm   | 19 mm    | 0.1 kg      |
| ELLCS1         | 64mm   | 22 mm    | 0.14 kg     |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE