

# Swing-Out Panel



Swing-Out Panels allow a front-mounted panel to pivot out of an enclosure frame opening. This accessory includes a panel and all the necessary hardware. Panels provide 170 degrees of rotation, with the capability to hinge from the right or left side.

## FEATURES

Swing-Out Panels are available for 600-, 700- and 800-mm wide enclosures

Spring-loaded pivot post allows for easy installation

Hinge blocks are anodized black; supports and panel have a painted white finish

Quarter-turn latches are provided to secure the Swing-Out Panel in the closed position

Panels provide 170 degrees of rotation, with the capability to hinge from the right or left side.

All necessary mounting hardware included

## SPECIFICATIONS

**Thickness:** 2.66mm  
**Finish:** Powder Coated  
**Color:** White

Table 1/1

| Catalog Number | Article Number | Material   | Fits Frame Width | Quick Ship |
|----------------|----------------|------------|------------------|------------|
| PSP146         | 91260          | Mild Steel | 600mm            | No         |
| PSP148         | 91920          | Mild Steel | 800mm            | No         |
| PSP166         | 91270          | Mild Steel | 600mm            | No         |
| PSP168         | 91930          | Mild Steel | 800mm            | No         |
| PSP186         | 91280          | Mild Steel | 600mm            | No         |
| PSP188         | 91940          | Mild Steel | 800mm            | No         |
| PSP206         | 91830          | Mild Steel | 600mm            | No         |
| PSP208         | 91950          | Mild Steel | 800mm            | No         |
| PSP226         | 91840          | Mild Steel | 600mm            | No         |
| PSP228         | 91960          | Mild Steel | 800mm            | No         |
| PSP76          | 91250          | Mild Steel | 600mm            | No         |
| PSP78          | 91910          | Mild Steel | 800mm            | No         |
| PSP147         | 91860          | Mild Steel | 700mm            | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**