


U-profile Front Panel, Shieldable, D-Sub Cutouts



U-profile front panel with cutout for D-Sub connectors.
Shieldable for textile EMC gasket.

CERTIFICATIONS



FEATURES

U-profile, front panel, Al, 2.5 mm, front anodized, rear conductive

For EMC textile gasket

SPECIFICATIONS

Depth (D):	2.5mm
Rack Height:	3U
Rack Width:	4HP
Material:	Aluminum
Finish:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel without Handle

Table 1/2

Catalog Number	Package Quantity	Mounting	Gasket Type	Front Finish	Rear Finish	Number of Pins
30849-751	1	Screw-on Front	Textile EMC	Anodized	Conductive	(3) 9
30849-750	1	Screw-on Front	Textile EMC	Anodized	Conductive	(2) 9
30849-752	1	Screw-on Front	Textile EMC	Anodized	Conductive	(1) 15
30849-754	1	Screw-on Front	Textile EMC	Anodized	Conductive	(1) 25
30849-753	1	Screw-on Front	Textile EMC	Anodized	Conductive	(2) 15
30849-755	1	Screw-on Front	Textile EMC	Anodized	Conductive	(2) 25
30849-749	1	Screw-on Front	Textile EMC	Anodized	Conductive	(1) 9

Table 2/2

Catalog Number	Treated Edges	Complies With	Height (H)	Width (W)	Quick Ship
30849-751	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	20mm	No
30849-750	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	20mm	No
30849-752	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	20mm	No
30849-754	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	20mm	No
30849-753	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	20mm	No
30849-755	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	20mm	No
30849-749	No	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	20mm	No

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please order textile EMC gasket separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

DIAGRAMS

