

Wire Spool



FEATURES

Spool with nVent CADDY Speed Link steel wire

Wire rope constructed from seven bundles of seven strands each of steel aircraft wire

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/1

Catalog Number	Article Number	Wire Rope Diameter	Length	Static Load
SLC15L1000SP	196001	1.5 mm	300m	195N
SLC15L50MSP	196023	1.5 mm	50m	195N
SLC2L1000SP	196002	2 mm	300m	440N
SLC2L100SP	196022	2 mm	100m	440N
SLC3L1000SP	196003	3 mm	300m	880N

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

