

EB-130 Main Terminal Clamp



CERTIFICATIONS



FEATURES

For use with EB-130 or EB-2X130 Earthing and Neutral Busbars

Quick and easy installation

RoHS compliant

SPECIFICATIONS

Material: Brass

Finish: Nickel Plated



Table 1/2

Catalog Number	Article Number	Conductor Size, IEC	Hole Size (HS)	Depth (D)	Height (H)	Width (W)
EB130CON70	568677	6 - 70 mm ² Stranded	5.5 mm	8mm	8 mm	31 mm
EB130CON35	568676	6 - 35 mm ² Stranded	5.5 mm	8mm	8 mm	22 mm

Table 2/2

Catalog Number	Article Number	Torque (TQ)	Unit Weight
EB130CON70	568677	2 N·m	0.01 kg
EB130CON35	568676	2 N·m	0.01 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE