

DAS and In-Building Wireless



HOFFMAN

STAY CONNECTED



Providing wireless coverage throughout a building is more important than ever. As more and more devices go wireless every day, the need to be connected grows too. Wireless users can't afford to drop calls or lose signal. This requires installing DAS or IBW systems and nVent HOFFMAN can help.

TYPE 4 AND 4X ENCLOSURES



CONTINUOUS HINGE WITH CLAMPS, TYPE 4

- 16 or 14 gauge steel
- External wall-mounting brackets for easy installation
- Removable door with continuous hinge for strength and ruggedness
- Collar studs for mounting optional panels



CONCEPT, TYPE 4 AND 12

- 18, 16 or 14 gauge steel
- Easy-to-remove and install hinge pins with built-in captivation clip
- Hidden hinges for clean, aesthetic appearance
- Door opens 210 degrees
- Mounting holes for optional external wall-mount brackets



FIBERGLASS FLAT COVER WITH LATCHES, TYPE 4X

- Compression-molded fiberglass construction
- Windows are clear polycarbonate
- Overlapping solid- and window-cover models are available
- Padlockable latches provide easy access and security



POLYPRO, TYPE 4X

- Polyester enclosure for superior UV resistance
- Chemical resistance against many contaminants
- Removable snap hinge cover
- Internal rail system and adjustable panel blocks allow for panel height adjustment



COMLINE OSP PACKAGE, TYPE 4X

- Solar shield keeps enclosure cool when installed outdoors; can be removed for indoor installations
- Doorstop holds door in place during service
- Rack angles adjustable front-to-rear of cabinet
- Gland plates available with cutouts
- Pole mounting kits available

NETWORKING



VERSARACK

- Left or right hinging for application specificity
- Ideal for high-density cabling applications
- Flat pack packaging for easy transport
- Single tool assembly for fast installation



ACCESSPLUS

- Double-hinged design for accessibility and security
- Easy, one person installation
- Gland plate retrofit
- Vertical cable management included with select models



PROTEK SINGLE-DOOR

- Robust, space-saving cabinet to protect, house and cool electronic components
- Premium seamless, foam-in-place gasket prevents contaminants from entering the cabinet
- Conserve floor space and locate electronics out of the way



SCREW-COVER, TYPE 1

- Unique keyhole screw slots in cover
- Available with or without knockouts
- Optional flush-mounted door frame
- Flat, removable covers fastened with plated steel screws
- Mounting holes on back of box



HINGED-COVER, TYPE 1

- Various sizes of easily removable concentric knockouts on all four sides
- Butt hinges
- Mounting holes on back of box



HOFFMAN excels at modifying and customizing products to your specifications. Contact your local HOFFMAN sales office or distributor for complete information.

CONTINUOUS HINGE WITH CLAMPS, TYPE 4

Catalog Number	H (in.)	W (in.)	D (in.)
A20H20BLP	20	16	8
A24H24ALP	24	24	6
A24H24BLP	24	24	8
A30H24ALP	30	24	6
A30H24BLP	30	24	8
A30H24CLP	30	24	10
A30H24DLP	30	24	12
A30H30BLP	30	30	8
A36H24BLP	36	24	8
A36H30BLP	36	30	8
A36H30CLP	36	30	10
A48H36DLP	48	36	10

CONCEPT, TYPE 4 AND 12

Catalog Number	H (in.)	W (in.)	D (in.)
CSD201610	20	16	10
CSD242010	24	20	10
CSD24206	24	20	6
CSD36248	36	24	8
CSD16168	16	16	8
CSD242412	24	24	12
CSD363612	36	36	12
CSD483612	48	36	12

FIBERGLASS FLAT COVER WITH LATCHES, TYPE 4X

Catalog Number	H (in.)	W (in.)	D (in.)
HJ1210HWPL2LG	11.68	9.69	4.62
HJ1412HWPL2LG	13.81	11.81	5.99
HJ1614HWPL2LG	15.81	13.81	5.99
HJ1816HWPL2LG	17.81	15.81	8.86
HJB1210HWPL2LG	11.68	9.69	4.62
HJB1412HWPL2LG	13.81	11.81	5.99
HJB1614HWPL2LG	15.81	13.81	5.99
HJB1816HWPL2LG	17.81	15.81	8.86

POLYPRO, TYPE 4X

Catalog Number	H (in.)	W (in.)	D (in.)	Cover Type
A12106PHCW	12.08	10.09	6.38	Window
A14128PHC	14.02	12.01	8.35	Solid
A14128PHCW	14.02	12.01	8.35	Window
A16148PHC	16.02	14.01	8.35	Solid
A16148PHCW	16.02	14.01	8.35	Window
A181610PHC	17.95	15.94	10.35	Solid
A181610PHCW	17.95	15.94	10.35	Window

COMLINE OSP PACKAGE, TYPE 4X

Catalog Number	H (in.)	W (in.)	D (in.)	Rack Units
ECL1207060P	47.24	27.56	23.62	25
ECL606050P	23.62	23.62	19.68	12
ECL906050P	35.43	23.62	19.68	18
ECL907060P	35.43	27.56	23.62	18
ECL907060PB	50.43	27.56	23.62	18

VERSARACK

Catalog Number	H (in.)	W (in.)	D (in.)	Rack Units
E19SWM12U12	27.80	20.91	12.28	12
E19SWM12U24	27.80	20.91	24.29	12
E19SWM20U12	41.81	20.91	12.28	20
E19SWM20U24	41.81	20.91	24.29	20
E19SWM25U12	50.59	20.91	12.28	25
E19SWM25U24	50.59	20.91	24.29	25

ACCESSPLUS

Catalog Number	H (in.)	W (in.)	D (in.)	Rack Units
Window Door Enclosure				
EWMW162418	16.75	24.41	18.2	8
EWMW162425	16.75	24.41	25.1	8
EWMW242425	23.62	23.62	25.09	12
EWMW362425	36.02	23.62	25.09	19
EWMW482425	48.03	23.62	25.09	26
EWMW242430	23.62	23.62	30.01	12
EWMW482430	48.03	23.62	30.01	26

Catalog Number	H (in.)	W (in.)	D (in.)	Rack Units
Window Door with Cable Manager Enclosure				
EWMW242825	23.62	27.56	25.09	12
EWMW362825	36.02	27.56	25.09	19
EWMW482825	48.03	27.56	25.09	26
Window Door with Gland Plate Enclosure				
EWMW362418	36.02	23.62	18.2	19
EWMW242425	23.62	23.62	25.09	12

Catalog Number	H (in.)	W (in.)	D (in.)	Rack Units
Window Door w/Cable Manager and Gland Plate Enclosure				
EWMW362825	36	28.31	25.1	19
EWMW482825	48	28.31	25.1	26

Catalog Number	H (in.)	W (in.)	D (in.)	Rack Units
Solid Door Enclosure				
EWMW242425	23.62	23.62	25.09	12
EWMW362425	36.02	23.62	25.09	19
EWMW482425	48.03	23.62	25.09	26

PROTEK SINGLE-DOOR

Catalog Number	H (in.)	W (in.)	D (in.)	Rack Units
PTRS242424G4A	24.09	23.62	24.02	12
PTRS242424X	24.09	23.62	24.02	12
PTRS242424XA	24.09	23.62	24.02	12
PTRS362424G4	36.3	23.62	24.02	19
PTRS362424G4A	36.3	23.62	24.02	19
PTRS362424X	36.3	23.62	24.02	19
PTRS362424XA	36.3	23.62	24.02	19
PTRS482424X	48.54	23.62	24.02	26
PTRS482424XA	48.54	23.62	24.02	26
PTRW242424G2	48.54	23.62	24.02	26
PTRW242424G2A	48.54	23.62	24.02	26
PTRW362424G2	36.3	23.62	24.02	19
PTRW362424G2A	36.3	23.62	24.02	19
PTRW362424GF	36.3	23.62	24.02	19
PTRW482424G2A	48.54	23.62	24.02	26

SCREW-COVER, TYPE 1

Catalog Number	H (in.)	W (in.)	D (in.)
ASE18X12X10NK	18	12	10
ASE18X12X8	18	12	8
ASE18X12X8NK	18	12	8
ASE24X12X10NK	24	12	10
ASE24X12X6NK	24	12	6
ASE24X12X8	24	12	8
ASE24X12X8NK	24	12	8
ASE24X18X10	24	18	10
ASE24X18X10NK	24	18	10
ASE24X20X8NK	24	20	8
ASE24X24X10	24	24	10
ASE24X24X10NK	24	24	10
ASE24X24X8	24	24	8
ASE24X24X8NK	24	24	8

HINGED-COVER, TYPE 1

Catalog Number	H (in.)	W (in.)	D (in.)
AHE10X10X6	10	10	6
AHE10X8X6	10	8	6
AHE12X10X6	12	10	6
AHE12X12X6	12	12	6
AHE16X12X6	16	12	6
AHE16X16X6	16	16	6
AHE18X12X6	18	12	6
AHE18X18X6	18	18	6
AHE24X18X6	24	18	6
AHE24X24X6	24	24	6
AHE30X24X6	30	24	6
AHE36X24X6	36	24	6
AHE36X24X8	36	24	8
A16N128LP	16	12	8.63
A16N128LP	16	12	8.62
A18N18CPL	18	18	10.62
A20N168LP	20	16	8.63
A20N168LP	20	16	8.62
A20N20ALP	20	20	6.62
A24N168LP	24	16	8.63
A24N16ALP	24	16	6.62
A24N2010LP	24	20	10.63
A24N208LP	24	28	8.63
A24N20ALP	24	20	6.62
A24N20ALP	24	20	6.62
A24N20BLP	24	20	8.63
A24N20CLP	24	20	10.62
A30N2412LP	30	24	12.63
A30N246LP	30	24	6.63
A30N248LP	30	24	8.63
A30N24ALP	30	24	6.62
A30N24BLP	30	24	8.62
A30N24CLP	60	24	10.62
A30N24DLP	30	24	12.62
A36N248LP	36	24	8.63
A36N24ALP	36	24	6.62
A36N24BLP	36	24	8.62
A36N308LP	36	30	8.63
A36N308LP	36	30	8.62

For a complete size listing, please contact your HOFFMAN representative or refer to nVent.com/HOFFMAN



nVent.com

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER