

# QTVR Self-Regulating Heating Cable



nVent RAYCHEM QTVR self-regulating trace heating cables are suitable for freeze protection of large pipes/vessels with high heat loss, and for process temperature maintenance applications without steam-cleaning requirements, up to 225 °F/110 °C. The fluoropolymer outer jacket (-CT) provides high chemical resistance against aggressive organics and corrosives.

## FEATURES

Simplified design for hazardous areas: unconditional T4 class

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

## SPECIFICATIONS

|                                                                       |                          |
|-----------------------------------------------------------------------|--------------------------|
| <b>Max Maintain or Continuous Exposure Temperature, Power On/Off:</b> | 110 °C                   |
| <b>Max Intermittent Exposure Temperature, Power On/Off:</b>           | 110 °C                   |
| <b>Supply Voltage:</b>                                                | 200 – 277 V              |
| <b>Ground Path Type:</b>                                              | Braid                    |
| <b>Outer Jacket Material:</b>                                         | Fluoropolymer            |
| <b>Area Classification:</b>                                           | Non-Hazardous; Hazardous |

Table 1/1

| Catalog Number | Item Name  | Nominal Power Output @ 10°C, 230V |
|----------------|------------|-----------------------------------|
| 040615-000     | 15QTVR2-CT | 51 W/m                            |
| 391991-000     | 10QTVR2-CT | 38 W/m                            |
| 988967-000     | 20QTVR2-CT | 64 W/m                            |

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### **Europe, Middle East, Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### **Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### **Latin America**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**