


## Varistar 19" Panel/Slide Mount



Slide mounts with adjustable increments.

### CERTIFICATIONS



### FEATURES

Depth-adjustable in 25 mm increments

In accordance with IEC 60297-1 (DIN 41 494, Part 1)

Assembly in 600 mm wide cabinets directly on the frame

For 800 mm width adapter bracket for reduced width is necessary, for partial-height mounting depth members are necessary

Dimensions are engraved in U increments (1 ... 52 U)

Made of Steel, 2 mm thick

Subsequent assembly possible

## SPECIFICATIONS

**Product Type:** Slide Mount

**Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Height | Finish        | Package Quantity | Color      | Color Code |
|----------------|-------------|--------|---------------|------------------|------------|------------|
| 23130-011      | 24U         | 1200mm | Powder Coated | 2                | Black Grey | RAL 7021   |
| 23130-012      | 29U         | 1400mm | Powder Coated | 2                | Black Grey | RAL 7021   |
| 23130-013      | 33U         | 1600mm | Powder Coated | 2                | Black Grey | RAL 7021   |
| 23130-014      | 38U         | 1800mm | Powder Coated | 2                | Black Grey | RAL 7021   |
| 23130-015      | 42U         | 2000mm | Powder Coated | 2                | Black Grey | RAL 7021   |
| 23130-016      | 47U         | 2200mm | Powder Coated | 2                | Black Grey | RAL 7021   |
| 23130-017      | 8U          | 400mm  | Powder Coated | 2                | Black Grey | RAL 7021   |
| 23130-018      | 12U         | 550mm  | Powder Coated | 2                | Black Grey | RAL 7021   |
| 23130-019      | 16U         | 750mm  | Powder Coated | 2                | Black Grey | RAL 7021   |
| 23130-020      | 20U         | 900mm  | Powder Coated | 2                | Black Grey | RAL 7021   |
| 23130-021      | 24U         | 1200mm | Powder Coated | 2                | Light Grey | RAL 7035   |
| 23130-022      | 29U         | 1400mm | Powder Coated | 2                | Light Grey | RAL 7035   |
| 23130-023      | 33U         | 1600mm | Powder Coated | 2                | Light Grey | RAL 7035   |

| CatalogNumber | Rack Height | Height | Finish               | Package Quantity | Color      | Color Code |
|---------------|-------------|--------|----------------------|------------------|------------|------------|
| 23130-024     | 38U         | 1800mm | Powder Coated        | 2                | Light Grey | RAL 7035   |
| 23130-025     | 42U         | 2000mm | Powder Coated        | 2                | Light Grey | RAL 7035   |
| 23130-026     | 47U         | 2200mm | Powder Coated        | 2                | Light Grey | RAL 7035   |
| 23130-027     | 8U          | 400mm  | Powder Coated        | 2                | Light Grey | RAL 7035   |
| 23130-028     | 12U         | 550mm  | Powder Coated        | 2                | Light Grey | RAL 7035   |
| 23130-029     | 16U         | 750mm  | Powder Coated        | 2                | Light Grey | RAL 7035   |
| 23130-030     | 20U         | 900mm  | Powder Coated        | 2                | Light Grey | RAL 7035   |
| 23130-031     | 24U         | 1200mm | Aluminum-Zinc Plated | 2                |            |            |
| 23130-032     | 29U         | 1400mm | Aluminum-Zinc Plated | 2                |            |            |
| 23130-033     | 33U         | 1600mm | Aluminum-Zinc Plated | 2                |            |            |
| 23130-034     | 38U         | 1800mm | Aluminum-Zinc Plated | 2                |            |            |
| 23130-035     | 42U         | 2000mm | Aluminum-Zinc Plated | 2                |            |            |
| 23130-036     | 47U         | 2200mm | Aluminum-Zinc Plated | 2                |            |            |
| 23130-037     | 8U          | 400mm  | Aluminum-Zinc Plated | 2                |            |            |
| 23130-038     | 12U         | 550mm  | Aluminum-Zinc Plated | 2                |            |            |
| 23130-039     | 16U         | 750mm  | Aluminum-Zinc Plated | 2                |            |            |
| 23130-040     | 20U         | 900mm  | Aluminum-Zinc Plated | 2                |            |            |
| 23130-570     | 52U         | 2450mm | Powder Coated        | 2                | Black Grey | RAL 7021   |

| CatalogNumber | Rack Height | Height | Finish               | Package Quantity | Color      | Color Code |
|---------------|-------------|--------|----------------------|------------------|------------|------------|
| 23130-588     | 52U         | 2450mm | Aluminum-Zinc Plated | 2                | Black Grey | RAL 7021   |

Table 2/2

| Catalog Number | Length | Package Unit | Quick Ship |
|----------------|--------|--------------|------------|
| 23130-011      | 1095mm | Pair         | No         |
| 23130-012      | 1295mm | Pair         | No         |
| 23130-013      | 1495mm |              | No         |
| 23130-014      | 1695mm | Pair         | No         |
| 23130-015      | 1895mm | Pair         | No         |
| 23130-016      | 2095mm | Pair         | No         |
| 23130-017      | 395mm  |              | No         |
| 23130-018      | 545mm  |              | No         |
| 23130-019      | 745mm  |              | No         |
| 23130-020      | 895mm  |              | No         |
| 23130-021      | 1095mm |              | No         |
| 23130-022      | 1295mm |              | No         |
| 23130-023      | 1495mm |              | No         |
| 23130-024      | 1695mm |              | No         |
| 23130-025      | 1895mm |              | No         |
| 23130-026      | 2095mm |              | No         |

| Catalog Number | Length | Package Unit | Quick Ship |
|----------------|--------|--------------|------------|
| 23130-027      | 395mm  |              | No         |
| 23130-028      | 545mm  |              | No         |
| 23130-029      | 745mm  |              | No         |
| 23130-030      | 895mm  |              | No         |
| 23130-031      | 1095mm | Pair         | No         |
| 23130-032      | 1295mm | Pair         | No         |
| 23130-033      | 1495mm |              | No         |
| 23130-034      | 1695mm | Pair         | No         |
| 23130-035      | 1895mm | Pair         | No         |
| 23130-036      | 2095mm | Pair         | No         |
| 23130-037      | 395mm  |              | No         |
| 23130-038      | 545mm  |              | No         |
| 23130-039      | 745mm  |              | No         |
| 23130-040      | 895mm  |              | No         |
| 23130-570      | 2345mm |              | No         |
| 23130-588      | 2345mm |              | No         |

## ADDITIONAL PRODUCT DETAILS

For 19" partial-height mounting depth members are necessary.

Metric panel/slide mounts available on request.

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**