

300 Universal Beam Clamp



CERTIFICATIONS







FEATURES

Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society (MSS) SP-58 (Type 19 and 23)

SPECIFICATIONS

Material: Cast Iron


Finish: Electrogalvanized


Table 1/1					
Catalog Number	Flange Thickness (FT)	A	Torque (TQ)	Static Load 1 (F1)	Static Load 2 (F2)
3000037EG	19.05 mm Max	28.5 mm	7 N·m	2200N	1100N
3000050EG	19.05 mm Max	28.57 mm	10.85 N·m	4200N	3400N

ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

