

nVent CADDY Cat HP J-Hook with C Purlin Clip



CERTIFICATIONS





FEATURES

Hammer-on or install from the floor with the VAFT tool

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Rounded edges on J-Hooks provide proper bend radius support for high performance data cables

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

SPECIFICATIONS

Finish: Pregalvanized;nVent CADDY Armour

Material: Steel; Spring Steel

Table 1/2							
Catalog Number	Article Number	Diameter (Ø)	Area	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	
CAT32HPVF14	181146	50 mm	2561mm²	90	60	35	

CatalogNumber	Article Number	Diameter (Ø)	Area	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	Cable Capacity, Cat 6A
CAT21HPVF14	181249	33.3 mm	1174mm²	50	40	25
CAT48HPVF14	181147	75 mm	5974mm²	200	150	80
CAT16HPVF14	181145	25 mm	690mm²	20	15	10
CAT64HPVF14	181148	100 mm	9987mm²	330	220	140


Table 2/2							
Catalog Number	Article Number	Flange Thickness (FT)	Static Load				
CAT32HPVF14	181146	1.5 - 6 mm	270N				
CAT21HPVF14	181249	1.5 - 6 mm	270N				
CAT48HPVF14	181147	1.5 - 6 mm	270N				
CAT16HPVF14	181145	1.5 - 6 mm	270N				
CAT64HPVF14	181148	1.5 - 6 mm	270N				

ADDITIONAL PRODUCT DETAILS

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

