

# nVent CADDY Speed Link SLS with Threaded Stud End



## CERTIFICATIONS



## FEATURES

Complete system includes wire, locking device and pre-assembled threaded stud end fitting

Attaches to structures with threaded anchors or devices with threaded hole

Finger tightening of nut secures the locking device into position without tools

Installs in strut profiles without the need to insert fingers or tools into the strut

## SPECIFICATIONS

|                                   |                                |
|-----------------------------------|--------------------------------|
| <b>Wire Rope Diameter:</b>        | 2 mm                           |
| <b>Static Load Safety Factor:</b> | 5:1                            |
| <b>Finish:</b>                    | Electrogalvanized              |
| <b>Material:</b>                  | Steel;Polypropylene;Zinc Alloy |
| <b>Complies With:</b>             | SMACNA HVAC-DCS                |

Table 1/1

| Catalog Number | Wire Rope Length | Rod Size (RS) | Screw Length (L) | Static Load |
|----------------|------------------|---------------|------------------|-------------|
|----------------|------------------|---------------|------------------|-------------|

|             |    |      |      |      |
|-------------|----|------|------|------|
| SLS2L3SE250 | 3m | 0.25 | 25mm | 270N |
| SLS2L2SE250 | 2m | 0.25 | 25mm | 270N |
| SLS2L5SE250 | 5m | 0.25 | 25mm | 270N |


**Slot Size (SS):** 8 x 6.5 mm - 8 x 10 mm  
**Hole Size (HS):** 8 - 10 mm  
**Width (W):** 16 mm  
**Height 2 (H2):** 43.5mm  
**Height 1 (H1):** 53mm  
**Thread Size (TS):** M8  
**Thickness (T):** 4 mm Max

## ADDITIONAL PRODUCT DETAILS

The 2 mm locking device is compatible with C-Channel Types E0 and E0L.

Total load per wire on a multi-tier trapeze must not exceed static load.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

