

# Crimping Compression Tool, Hydraulic

## Data Solutions

### CATALOG NUMBER

---

**M2H**



### FEATURES

---

Wide cross section range

Ergonomic design

Lightweight and easy to use

Includes easy-to-carry custom case

### PRODUCT ATTRIBUTES

---

Article Number: 716905

Applied Force: 60kN

System: Hand hydraulic

Dies: RKM2 series; PKM2 series

Crimping Shape: Hexagon

Conductor Size: #10 Stranded - 600 kcmil Stranded; 6 mm<sup>2</sup> Stranded - 300 mm<sup>2</sup> Stranded

### WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**