

# ProLine Tie-Down Reducing Bracket

## Data Solutions



The ProLine Tie-Down Reducing Bracket provides a convenient tie down for vertical or horizontal cable management. It allows front-to-back cable pass through while supporting optional D-Rings and wire management spools. The bracket mounts on either the left or right side of 700- and 800-mm cabinets between the frame and the rack angle to create vertical wiring space. Please note the mounting hardware and 10 VELCRO® Cable Wraps included.

### FEATURES

The ProLine Tie-Down Reducing Bracket provides a convenient tie down for vertical or horizontal cable management

It allows front-to-back cable pass through while supporting optional D-Rings and wire management spools

The bracket mounts on either the left or right side of 700- and 800-mm cabinets between the frame and the rack angle to create vertical wiring space

Please note the mounting hardware and 10 Cable Wraps included

### SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Width | Material   | Finish        | Color     | Color Code |
|----------------|----------------|-------|------------|---------------|-----------|------------|
| PRBTD205       | 16003          | 50mm  | Mild Steel | Powder Coated | Jet Black | RAL 9005   |
| PRBTD125       | 16001          | 50mm  | Mild Steel | Powder Coated | Jet Black | RAL 9005   |
| PRBTD2010      | 16004          | 100mm | Mild Steel | Powder Coated | Jet Black | RAL 9005   |
| PRBTD1210      | 16002          | 100mm | Mild Steel | Powder Coated | Jet Black | RAL 9005   |

Table 2/2

| Catalog Number | Article Number | Thickness | Fits Cabinet Height |
|----------------|----------------|-----------|---------------------|
| PRBTD205       | 16003          | 2.66mm    | 2000mm              |
| PRBTD125       | 16001          | 2.66mm    | 1200mm              |
| PRBTD2010      | 16004          | 2.66mm    | 2000mm              |
| PRBTD1210      | 16002          | 2.66mm    | 1200mm              |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**