

Telecom Main Grounding Busbar



CERTIFICATIONS



FEATURES

Meets TIA-607-C and TIA-607-D and conforms to BICSI® recommendations

Complies with NEMA® standards

Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)

Telecom grounding busbar splice kits are available to extend the length of the busbar

SPECIFICATIONS

Thickness (T): 6.35 mm
Width (W): 101.6 mm
Material: Copper

Table 1/2


Catalog Number	Tin Plating	Length 1 (L1)	Length 2 (L2)	Hole Size 1 Number of Pairs	Hole Size 2 Number of Pairs	A
TMGBA12L15P	No	305 mm	229 mm	15	3	25.4 mm

CatalogNumber	Tin Plating	Length 1 (L1)	Length 2 (L2)	Hole Size 1 Number ofPairs	Hole Size 2 Number ofPairs	A
TMGBA12L15PT	Yes	305 mm	229 mm	15	3	25.4 mm
TMGBA16L19P	No	394 mm	229 mm	19	3	25.4 mm
TMGBA16L19PT	Yes	394 mm	229 mm	19	3	25.4 mm
TMGBA18L23P	No	451 mm	229 mm	23	3	25.4 mm
TMGBA18L23PT	Yes	451 mm	229 mm	23	3	25.4 mm
TMGBA20L27P	No	508 mm	229 mm	27	3	25.4 mm
TMGBA20L27PT	Yes	508 mm	229 mm	27	3	25.4 mm
TMGBA24L33P	No	610 mm	457 mm	33	5	25.4 mm
TMGBA24L33PT	Yes	610 mm	457 mm	33	5	25.4 mm
TMGBA29L41P	No	737 mm	457 mm	41	5	25.4 mm
TMGBA29L41PT	Yes	737 mm	457 mm	41	5	25.4 mm

Table 2/2			
Catalog Number	B	C	D
TMGBA12L15P	28.6 mm	15.9 mm	15.9 mm
TMGBA12L15PT	28.6 mm	15.9 mm	15.9 mm
TMGBA16L19P	28.6 mm	15.9 mm	15.9 mm
TMGBA16L19PT	28.6 mm	15.9 mm	15.9 mm

Catalog Number	B	C	D
TMGBA18L23P	28.6 mm	15.9 mm	15.9 mm
TMGBA18L23PT	28.6 mm	15.9 mm	15.9 mm
TMGBA20L27P	28.6 mm	15.9 mm	15.9 mm
TMGBA20L27PT	28.6 mm	15.9 mm	15.9 mm
TMGBA24L33P	28.6 mm	15.9 mm	15.9 mm
TMGBA24L33PT	28.6 mm	15.9 mm	15.9 mm
TMGBA29L41P	28.6 mm	15.9 mm	15.9 mm
TMGBA29L41PT	28.6 mm	15.9 mm	15.9 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE