

Dual-Access Safety Lockout



Dual-Access Safety Lockouts provide a means of using two padlocks on a secured power source. Either padlock can be removed enabling power to be interrupted and enclosure accessed. Padlock holes are .38-in. (10-mm) in diameter.

FEATURES

Padlock is not included

Catalog number ASLDAC includes a 10.00-in. (254-mm) plated steel chain

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
ASLDAC	11390	Mild Steel	Powder Coated	Signal Red	RAL 3001	3.4mm
ASLDA	11380	Mild Steel	Powder Coated	Signal Red	RAL 3001	3.4mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE