

U-Connector Lay-in Painted Galvanized



Lay-in Painted Galvanized U-Connectors are used to rigidly join fittings to lay-in wireway straight sections. Top swings aside to retain the lay-in feature. One U-connector required at each wireway joint except telescope fittings, panel adapters, open adapters, closure plates or reducers.

FEATURES

Lay-in Painted Galvanized U-Connectors are used to rigidly join fittings to lay-in wireway straight sections

Top swings aside to retain the lay-in feature

One U-connector required at each wireway joint except telescope fittings, panel adapters, open adapters, closure plates or reducers

SPECIFICATIONS

- Color Code:

ANSI 61
- Finish:

Galvanized; Powder Coated
- Color:

Gray
- Material:

Mild Steel

Table 1/1						
Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
F44T3RUC	43549	U-Connector	102mm	102mm	1.52mm	No
F66T3RUC	43699	U-Connector	152mm	152mm	1.52mm	No
F88T3RUC	43859	U-Connector	203mm	203mm	1.9mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE