

# EuropacPRO 19" Subrack Kit for Backplane, Slide Rail, Retrofit Shielding



Non-shielded subrack for backplane, subrack can be assembled on slide rails to support the subrack inside a cabinet.

## CERTIFICATIONS



## FEATURES

Subrack with side panel type F ("Flexible"), 19" bracket is depth-adjustable

Subrack can be used with slide rails

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 11 kg

Threaded insert, insulation strip pre-fitted

## SPECIFICATIONS

|                       |                      |
|-----------------------|----------------------|
| <b>Material:</b>      | Aluminum             |
| <b>Finish:</b>        | Anodized; Passivated |
| <b>EMC Shielding:</b> | No                   |
| <b>Product Type:</b>  | Subrack/Chassis      |

Table 1/2

| Catalog Number | Rack Height | Depth | Package Quantity | For Mounting | Board Depth | EMC Gasket Type |
|----------------|-------------|-------|------------------|--------------|-------------|-----------------|
|----------------|-------------|-------|------------------|--------------|-------------|-----------------|

|           |    |       |   |           |                                     |                 |
|-----------|----|-------|---|-----------|-------------------------------------|-----------------|
| 24553-132 | 3U | 235mm | 1 | Backplane | 160mm,<br>220mm                     | Stainless Steel |
| 24553-133 | 3U | 295mm | 1 | Backplane | 160mm,<br>220mm,<br>280mm           | Stainless Steel |
| 24553-134 | 3U | 355mm | 1 | Backplane | 160mm,<br>220mm,<br>280mm,<br>340mm | Stainless Steel |
| 24553-432 | 6U | 235mm | 1 | Backplane | 160mm,<br>220mm                     | Stainless Steel |
| 24553-433 | 6U | 295mm | 1 | Backplane | 160mm,<br>220mm,<br>280mm           | Stainless Steel |
| 24553-434 | 6U | 355mm | 1 | Backplane | 160mm,<br>220mm,<br>280mm,<br>340mm | Stainless Steel |

Table 2/2

| Catalog Number | Handle Included | Mounting | Complies With   | Rack Width | Static Load | Quick Ship |
|----------------|-----------------|----------|-----------------|------------|-------------|------------|
| 24553-132      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        | No         |
| 24553-133      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        | No         |
| 24553-134      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        | No         |
| 24553-432      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        | No         |
| 24553-433      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        | No         |
| 24553-434      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        | No         |

## ADDITIONAL PRODUCT DETAILS

Alternative product for older EuropacLab and Europac subrack series.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**