nVent SCHROFF

We connect and protect

Novastar Depth Member



Depth member which is adjustable in 1 U increments in the height.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

For assembly on cabinet uprights

Adjustable in 1 U increments

SPECIFICATIONS

Product Type: Bracket

Table 1/2

Catalog Number	Depth	Material	Finish	Package Quantity	Type	Package Unit
27230-167	500mm	Steel	Aluminum-Zinc Plated	2	Depth Member	Pair
27230-168	600mm	Steel	Aluminum-Zinc Plated	2	Depth Member	Pair
27230-169	800mm	Steel	Aluminum-Zinc Plated	2	Depth Member	Pair
27230-170	900mm	Steel	Aluminum-Zinc Plated	2	Depth Member	Pair

CatalogNumber	Depth	Material	Finish	Package Quantity	Type	Package Unit
27230-171	1000mm	Steel	Aluminum-Zinc Plated	2	Depth Member	Pair

Table 2/2

Catalog Number	Quick Ship
27230-167	No
27230-168	No
27230-169	No
27230-170	No
27230-171	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.