

# PSU 19" DC/DC Coolpower 100 W, Single



Pluggable 19" Power Supplies with H15 connector for fanless applications.

## **CERTIFICATIONS**





## **FEATURES**

Wide input voltage range from 20 to 72 VDC

Galvanic separation between primary and secondary circuits

High power density

External ON/OFF

## **SPECIFICATIONS**

Table 1/2									
Catalog Number	Туре	Input Voltage DC	Power	Number of Output Voltages	Voltage 1	Current 1			
13103-003	19" DC/DC Converter	20 - 72V	102W	1	12V	8.5A			
13103-004	19" DC/DC Converter	20 - 72V	100W	1	15V	6.7A			
13103-002	19" DC/DC Converter	20 - 72V	100W	1	5V	20A			

Table 2/2								
Catalog Number	Rack Height	Rack Width	Depth	Package Quantity	Quick Ship			
13103-003	3U	6НР	171.93mm	1	No			
13103-004	3U	6НР	171.93mm	1	No			
13103-002	3U	6НР	171.93mm	1	No			

### ADDITIONAL PRODUCT DETAILS

Please order front panel separately.

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

# **Europe**

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

## Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

## Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**