


MI PDU, 1U, 60A(48A), 208V, 3P Delta, 6 CB, (9)4-in-1

Data Solutions

CATALOG NUMBER

EN1963



The Advantage Series Input Metered PDU family offers energy metering with advanced power and environmental monitoring options. Comprehensive monitoring at both the input phase and circuit breaker levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

PRODUCT ATTRIBUTES

Product Family: Enlogic

Product Type: Socket Strip

Socket Type: (9) C13/C15/C19/C21

Color: Black

Switched Outlets: No

Circuit Breaker: 20 A

Length: 44mm

Power Rating: 17.3 kVA

Circuit Breaker Quantity: 6

Input Voltage: 208V

Phase: 3 PH Delta

Number of Poles: 2

Output Voltage: 208VAC

Nominal Voltage: 208V

Plug Type: IEC 60309 460P9 (IP44)

Removable Input Cable: No

Amperage (Derated Amperage): 60 A (48 A)

Finish: Powder Coated

Rack Units: 1U

Material: Steel

Type: Intelligent PDU

Height: 44mm

Width: 444mm

Depth: 269mm

Weight: 7kg

Package Quantity: 1

Input Cable Length: 1.8m

Interrupt Rating: 10kAIC

ADDITIONAL PRODUCT DETAILS

43 mm L x 444 mm W x 269 mm D, (269 mm D at CB)

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE