


Copper Ground Plate with Cable Attachments



CERTIFICATIONS



FEATURES

Bonding plates provide mechanical attachment points to ground plate

Listed to UL® 96

SPECIFICATIONS

Material: Copper

Table 1/1

Catalog Number	Number of Cable Attachments	Width (W)	Length (L)	Thickness (T)	Certifications
LPC756	2	609.6 mm	609.6mm	0.81 mm	E202878-Combined_CoC, E202878-Combined_CoC
LPC755	1	914.4 mm	914.4mm	0.81 mm	E202878-Combined_CoC, E202878-Combined_CoC

Catalog Number	Number of Cable Attachments	Width (W)	Length (L)	Thickness (T)	Certifications
LPC754	1	457.2 mm	457.2mm	0.81 mm	E202878-Combined_CoC, E202878-Combined_CoC
LPC750	2	304.8 mm	609.6mm	0.81 mm	E202878-Combined_CoC, E202878-Combined_CoC
LPC753	1	304.8 mm	609.6mm	0.81 mm	
LPC752	2	914.4 mm	914.4mm	0.81 mm	E202878-Combined_CoC, E202878-Combined_CoC
LPC751	2	457.2 mm	457.2mm	0.81 mm	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE