

# ISONV Equipotential Bond Kit



## FEATURES

Used with ISONV lower terminations when equipotential bonding is required

Crimps to copper earthing conductor

## SPECIFICATIONS

**Material:** Stainless Steel 304 (EN 1.4301);Copper

**Finish:** Tinned

Table 1/1

Catalog Number	Conductor Type	Conductor Size
ISONVEBL50	ISONV50	16 mm <sup>2</sup> Stranded
ISONVEBL70	ISONV70	16 mm <sup>2</sup> Stranded

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**