

# **RRCB Round Braid in Coil, Plain Copper**



## **CERTIFICATIONS**



#### **FEATURES**

Braids in coil are mainly used for power distribution or earthing applications

Non-magnetic material

#### **SPECIFICATIONS**

Material: Copper

Table 1/2						
Catalog Number	Article Number	Nominal Current	Cross Section	Number of Wires	Wire Diameter	Length
RRCB15-25	557440	150A	25mm²	1416	0.15mm	25m
RRCB15-75	557470	300A	75mm²	4236	0.15mm	25m
RRCB15-10	557420	75A	10mm²	560	0.15mm	25m
RRCB15-30	557450	180A	30mm²	1680	0.15mm	25m

CatalogNumber	Article Number	Nominal Current	Cross Section	Number of Wires	Wire Diameter	Length
RRCB15-16	557430	120A	16mm²	900	0.15mm	25m
RRCB15-50	557460	250A	50mm²	2820	0.15mm	25m
RRCB15-6	557400	45A	6mm²	352	0.15mm	25m

Table 2/2						
Catalog Number	Article Number	Diameter	Unit Weight			
RRCB15-25	557440	8 mm	0.25 kg			
RRCB15-75	557470	14 mm	0.75 kg			
RRCB15-10	557420	5 mm	0.1 kg			
RRCB15-30	557450	9 mm	0.3 kg			
RRCB15-16	557430	6 mm	0.16 kg			
RRCB15-50	557460	11 mm	0.5 kg			
RRCB15-6	557400	4 mm	0.06 kg			

## **ADDITIONAL PRODUCT DETAILS**

Unit weight is per meter (3.28').

#### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE