

# Ground Mounted Plinth, PGM



Cables can be easily routed through the ground plinth, which is mounted underground, allowing cables to be channelled and therefore, wired more quickly.

## FEATURES

Description: Ground mounted plinth 1000 mm height. Excavation depth: 700-950 mm.

Material: 2 mm galvanized steel.

Finish: RAL 7035 polyester powder coated.

Pack quantity: 1 kit of ground mounted plinth.

## SPECIFICATIONS

**Thickness:** 2mm  
**Finish:** Galvanized  
**Material:** Galvanized Steel  
**Color:** Light Gray  
**Color Code:** RAL 7035

Table 1/1

| Catalog Number | Height | Width  | Depth | Enclosure Material | Product Family | Quick Ship |
|----------------|--------|--------|-------|--------------------|----------------|------------|
| PGM10064       | 1000mm | 600mm  | 400mm | Aluminum           | Free-Standing  | No         |
| PGM10066       | 1000mm | 600mm  | 600mm | Aluminum           | Free-Standing  | No         |
| PGM10084       | 1000mm | 800mm  | 400mm | Aluminum           | Free-Standing  | No         |
| PGM10086       | 1000mm | 800mm  | 600mm | Aluminum           | Free-Standing  | No         |
| PGM10124       | 1000mm | 1200mm | 400mm | Aluminum           | Free-Standing  | No         |
| PGM10126       | 1000mm | 1200mm | 600mm | Aluminum           | Free-Standing  | No         |
| PGM10184       | 1000mm | 1800mm | 400mm | Aluminum           | Free-Standing  | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**