

# ProLine G2 Side Cover



ProLine G2 Solid Sides enclose the open sides of the modular enclosure frame and have innovative design elements incorporated to ensure fast installation and enhanced structural support.

## FEATURES

---

Hinge hanger on top for easy alignment

Formed steel hems on the sides of the covers for enhanced structural support and to protect user from sharp edges

Seamless polyurethane gasket (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Attach to enclosure frame with low-profile, flat head screws

Door can be reversed without removing the side covers

Used on the sides of the ProLine G2 frame

Not suitable as a barrier between enclosures (instead use the ProLine G2 barrier panel)

Two grounding studs

All mounting hardware included

Side Covers are finished with paint over plated surfaces

## SPECIFICATIONS

**Color:** Light Gray

**Color Code:** RAL 7035

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
P2CS104	33686	983mm	364mm	20mm	Mild Steel	Powder Coated
P2CS124	33653	1183mm	364mm	20mm	Mild Steel	Powder Coated
P2CS164	31327	1583mm	364mm	20mm	Mild Steel	Powder Coated
P2CS205	31342	1983mm	464mm	20mm	Mild Steel	Powder Coated
P2CS206	31344	1983mm	564mm	20mm	Mild Steel	Powder Coated
P2CS84	33685	783mm	364mm	20mm	Mild Steel	Powder Coated

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**