

Side Panels, SPM



These side panels will ensure that the ingress protection is maintained, which means that the electrical components will operate without any disturbances and protect personnel from injuries.

FEATURES

Description: Easy one man assembly. Sealed by an extruded, one piece polyurethane gasket and mounted with 8 screws and new patented retainers. Can be replaced by the side door DNS.

Material: 1.5 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: IP 55, TYPE 12, 13 in combination with MCS. IP66, TYPE 4, 12, 13 in combination with MCS-HP.

Pack quantity: 2 panels with mounting accessories.

SPECIFICATIONS

Thickness: 1.5mm
Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Enclosure Material	Quick Ship
SPM1106R5		1100mm	19mm	600mm	Mild Steel	No
SPM1606R5	SPM1606R5	1600mm	19mm	600mm	Mild Steel	No
SPM1406R5	SPM1406R5	1400mm	19mm	600mm	Mild Steel	No
SPM1808R5	SPM1808R5	1800mm	19mm	800mm	Mild Steel	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE