

# Etsirack Frame



Welded frame with metric grid holes in accordance with ETS 300119-3, with load capacity of 200 kg.

## CERTIFICATIONS



## FEATURES

Welded frame with metric grid holes in accordance with ETS 300119-3

Mounting height 81 SU

Static load-carrying capacity 200 kg

Back-to-back row layout is possible

In accordance with standards IEC 48 D and ETS 300 119

Top mounted cabling frame

## SPECIFICATIONS

|                        |                    |
|------------------------|--------------------|
| <b>Static Load:</b>    | 200kg              |
| <b>Product Type:</b>   | Cabinet/Rack Frame |
| <b>Material:</b>       | Steel              |
| <b>Frame Material:</b> | Steel              |

Table 1/2

| Catalog Number | Height | Width | Depth | Package Quantity | Color | Color Code |
|----------------|--------|-------|-------|------------------|-------|------------|
|----------------|--------|-------|-------|------------------|-------|------------|

|           |        |       |       |   |            |          |
|-----------|--------|-------|-------|---|------------|----------|
| 10125-010 | 2200mm | 600mm | 300mm | 1 | Light Grey | RAL 7035 |
| 10125-011 | 2200mm | 600mm | 300mm | 2 | Light Grey | RAL 7035 |

Table 2/2

| Catalog Number | Finish        | Type     | Quick Ship |
|----------------|---------------|----------|------------|
| 10125-010      | Powder Coated | Standard | No         |
| 10125-011      | Powder Coated | Standard | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**